

RackPower PDU, RP6xxx, 230/400 VAC, 3-phase

Energiebedrijven

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

KENMERKEN

RackPower RP6xxx Intelligent Power Distribution Units monitors input and outlet power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

User-defined power-on time delay or automatic power-on sequencing

SPECIFICATIES

Table 1/2

Catalogusnummer	Product Type	Socket Type	Kleur	Lengte	Voltage AC	Function
RP6950	Socket Strip	IEC C13, IEC C13/C19	Zwart	1826 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets

Catalogusnummer	Product Type	Socket Type	Kleur	Lengte	Voltage AC	Function
RP6850	Socket Strip	IEC C13, IEC C13/C19	Zwart	1780 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets
RP6450	Socket Strip	IEC C13, IEC C13/C19	Zwart	1490 mm	230 V	Input Monitored, Outlet Monitored, Switched Outlets

Table 2/2

Catalogusnummer	Diepte	Breedte
RP6950	75 mm	56 mm
RP6850	75 mm	56 mm
RP6450	75 mm	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE