

19" Fan Unit, 1 U, Speed Control and Monitoring

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICATIONS



CARACTERISTICAS

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Tensão de entrada AC	Tensão de entrada DC	Quantidade por embalagem	Acabamento	Material	Certifications
10713-098		24V min	1	Aluminum-Zinc Plated, Anodized	Aço, Alumínio	CE, EAC, RoHS
19713-006	230V		1	Aluminum-Zinc Plated, Anodized	Aço, Alumínio	CE, EAC, RoHS

Número de catálogo	Tensão de entrada AC	Tensão de entrada DC	Quantidade por embalagem	Acabamento	Material	Certifications
10713-099		24V min	1	Aluminum-Zinc Plated, Anodized	Aço, Alumínio	RoHS, CE, EAC
19713-121	230V		1	Aluminum-Zinc Plated, Anodized	Aço, Alumínio	RoHS, EAC

Table 2/2

Número de catálogo	Envio rápido
10713-098	Não
19713-006	Não
10713-099	Não
19713-121	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE