

Combined Mounting Kit for Chassis



The combined mounting enable the option to split a 6 U high subrack or case in 2 x 3 U and 6 U sections. Different versions are available.

CERTIFICATIONS



CARACTERÍSTICAS

Designed to accept Euroboards (100 mm high) and double Euroboards (233.35 mm high)

Subdivision of the 6 U assembly area into: 2 x 3 U, 1 x 6 U

ESPECIFICAÇÕES

Rack Height:	6U
Tipo:	Combined
Família de produtos:	EuropacPRO
Product Type:	Mounting Kit
Works With:	Subracks

Table 1/1

Número de catálogo	Quantidade por embalagem	Rack Width 1	Rack Width 2	Material	Envio rápido
24562-420	1	20HP	62HP	Aluminio, Liga de zinco	Não
24562-440	1	40HP	42HP	Aluminio, Liga de zinco	Não
24562-442	1	42HP	40HP	Aluminio, Liga de zinco	Não

Número de catálogo	Quantidade por embalagem	Rack Width 1	Rack Width 2	Material	Envio rápido
24562-484	1	84HP		Aluminio, Liga de zinco	Não
24562-463	1	63HP	19HP	Aluminio, Liga de zinco	Não

DETALHES ADICIONAIS DO PRODUTO

Please order separately: Front panel 6 U, 2 HP to cover the strut.

The following guide rails cannot be used: type "accessory", type "accessory, strengthened" and type "for 4.4" PCB".

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE