

# Varistar CP Base Plate, Multi-Piece

## Energiebedrijven

Multi piece base plate is assembled from inside.

Please order grounding, cover plate, brush strip or filter mat separately.

### KENMERKEN

To cover the base opening

The multi-part base plate is open at the rear (opening to rear 200 mm deep, no rear opening with 300 mm cabinet depth)

### SPECIFICATIES

Table 1/1

| Catalogusnummer | Breedte | Diepte  | Kleur      | Color Code | Materiaal | Product Type      |
|-----------------|---------|---------|------------|------------|-----------|-------------------|
| 21630-616       | 600 mm  | 600 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-617       | 600 mm  | 800 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-618       | 600 mm  | 900 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-619       | 600 mm  | 1000 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-620       | 600 mm  | 1100 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-621       | 600 mm  | 1200 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-802       | 600 mm  | 600 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-803       | 600 mm  | 800 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-804       | 600 mm  | 900 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |

| Catalogusnummer | Breedte | Diepte  | Kleur      | Color Code | Materiaal | Product Type      |
|-----------------|---------|---------|------------|------------|-----------|-------------------|
| 21630-805       | 600 mm  | 1000 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-806       | 600 mm  | 1100 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-807       | 600 mm  | 1200 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-622       | 800 mm  | 600 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-808       | 800 mm  | 600 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-623       | 800 mm  | 800 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-624       | 800 mm  | 900 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-625       | 800 mm  | 1000 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-626       | 800 mm  | 1100 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-627       | 800 mm  | 1200 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-809       | 800 mm  | 800 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-810       | 800 mm  | 900 mm  | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-811       | 800 mm  | 1000 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-812       | 800 mm  | 1100 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |
| 21630-813       | 800 mm  | 1200 mm | Black Grey | RAL 7021   | Staal     | Cabinet/Rack Base |

## ADDITIONAL PRODUCT DETAILS

Multi piece base plate is assembled from inside.

Please order grounding, cover plate, brush strip or filter mat separately.

## WAARSCHUWING

---

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van [www.nvent.com](http://www.nvent.com) of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**