

Varistar CP Perforated, Seismic Base Plate, EMC, for Rear Cable Ducting

Energiebedrijven

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

KENMERKEN

Installation from outside

Cutout at rear

60 mm deep

Cable ducting with IP 55 / EMC gasket

SPECIFICATIES

Table 1/2

Catalogusnummer	Breedte	Diepte	Kleur	Color Code	Voltoet aan	Materiaal
20630-325	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3	Staal
20630-326	600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3	Staal
20630-327	600 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3	Staal
20630-328	600 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3	Staal
20630-329	800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3	Staal
20630-330	800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3	Staal

Catalogusnummer	Breedte	Diepte	Kleur	Color Code	Voldoet aan	Materiaal
20630-331	800 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3	Staal
20630-332	800 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3	Staal

Table 2/2

Catalogusnummer	Product Type	Type	Works With
20630-325	Cabinet/Rack Base	Base Plate, Perforated	Varistar CP
20630-326	Cabinet/Rack Base	Base Plate, Perforated	Varistar CP
20630-327	Cabinet/Rack Base	Base Plate, Perforated	Varistar CP
20630-328	Cabinet/Rack Base	Base Plate, Perforated	Varistar CP
20630-329	Cabinet/Rack Base	Base Plate, Perforated	Varistar CP
20630-330	Cabinet/Rack Base	Base Plate, Perforated	Varistar CP
20630-331	Cabinet/Rack Base	Base Plate, Perforated	Varistar CP
20630-332	Cabinet/Rack Base	Base Plate, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

Please purchase the grounding kit separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE