

Varistar CP Swing Frame for 600 mm Width

Energiebedrijven

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° movement and flexible pivot point.

KENMERKEN

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" sub racks (maximum depth 200 mm)

120° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Kleur	Color Code	Hoogte	Materiaal	Product Type
21630-668	24 U	Black Grey	RAL 7021	1200 mm	Staal	Cabinet/Rack Frame
21630-670	29 U	Black Grey	RAL 7021	1400 mm	Staal	Cabinet/Rack Frame
21630-672	33 U	Black Grey	RAL 7021	1600 mm	Staal	Cabinet/Rack Frame
21630-674	38 U	Black Grey	RAL 7021	1800 mm	Staal	Cabinet/Rack Frame
21630-676	42 U	Black Grey	RAL 7021	2000 mm	Staal	Cabinet/Rack Frame
21630-678	47 U	Black Grey	RAL 7021	2200 mm	Staal	Cabinet/Rack Frame

Table 2/2

Catalogusnummer	Protection Rating	Breedte
21630-668	IP20	600 mm
21630-670	IP20	600 mm
21630-672	IP20	600 mm
21630-674	IP20	600 mm
21630-676	IP20	600 mm
21630-678	IP20	600 mm

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE