

Front Panel, Flat, With Slot for Stainless Steel EMC Gasket



Front panel, flat, with slot for stainless steel EMC gasket.

CERTIFICATIONS



CARACTERÍSTICAS

Flat front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For stainless steel gasket

ESPECIFICAÇÕES

Profundidade:	2.5mm
Rack Height:	4U
Material:	Aluminio
Acabamento:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Tipo:	Front Panel without Handle
EMC Shielding:	No (Retrofittable)

Table 1/2

Número de catálogo	Rack Width	Quantidade por embalagem	Instalação	EMC Gasket Type	Front Finish	Rear Finish
--------------------	------------	--------------------------	------------	-----------------	--------------	-------------

30846-681	42HP	1	Screw-on Front	Aço inoxidável	Anodized	Conductive
30846-682	63HP	1	Screw-on Front	Aço inoxidável	Anodized	Conductive

Table 2/2					
Número de catálogo	Treated Edges	Em conformidade com	Altura	Largura	Envio rápido
30846-681	Não	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	Não
30846-682	Não	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	319.7mm	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE