

Telescopic Slide Universal, Slim, 2 U

Slim Universal Telescopic Slide, 2 U.



CERTIFICATIONS



CARACTERISTICAS

Rail width k = 9.7 mm, max. installation width of extension/drawer w = 429 mm

Lateral mounting on the 19" uprights (19" plane remains free for fixing the extension/drawer)

Locking at full extension

Static load-carrying capacity per pair 46 - 57 kg

Extension length > 110 %

ESPECIFICAÇÕES

Material:	Aço
Product Type:	Telescopic Slide
Acabamento:	Chapa de Aço Zincada

Table 1/1

Número de catálogo	Length	Quantidade por embalagem	Static Load	Tipo	Envio rápido
20110-071	356mm	2	57kg	Universal	Não

Número de catálogo	Length	Quantidade por embalagem	Static Load	Tipo	Envio rápido
20110-074	508mm	2	55kg	Universal	Não
20110-077	610mm	2	46kg	Universal	Não
20110-073	457mm	2	55kg	Universal	Não
20110-075	559mm	2	46kg	Universal	Não
20110-072	406mm	2	55kg	Universal	Não
20110-076	584mm	2	46kg	Universal	Não

DETALHES ADICIONAIS DO PRODUTO

Universal telescopic Rails can also be fitted without additional components in non-standard applications, this also in other than 19" cabinets.

To mount on 19" plane please order assembly kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE