

Telescopic Screw Gun Box Strap



The nVent CADDY Telescopic Screw Gun Box Strap is a versatile and robust support inspired by installers in the UK to securely fasten electric boxes to in-wall studs. Its engineered profile guarantees an extra sturdy and durable connection to the box and studs while requiring a minimal amount of screws. Available in two sizes, the box strap accommodates most stud spacings without cumbersome and time-consuming rework.

CARACTERÍSTICAS

Engineered profile with a recessed cavity to provide extra sturdy connection to the box and prevent loosening over time, even with short 12 mm-long self-tapping screws

Improved design only requires a single screw per tab and two screws per box, saving up to 30% of installation time

Can mount multiple boxes

Notched and marked for easy identification and bending, tailored to UK market box depths

Improved design with stamped mm markings and pilot holes accelerates precise box conduit mounting between studs

V cut-out and line of pilot holes indicates a bar's center for a fast bracket leveling using a laser level

Pilot holes allow easy box attachment with a screwdriver

Requires only a screw gun to install

Can be mounted to face or inside of stud using a single screw per tab

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly

Unique, one-piece, break apart design

ESPECIFICAÇÕES

Acabamento: Pregalvanized

Material: Aço

Table 1/1

Número de catálogo	Número do artigo	Stud Spacing	Box Depth
TSGB1624UK	187202	355 - 655 mm	25mm, 35mm, 47mm

Número de catálogo	Número do artigo	Stud Spacing	Box Depth
TSGB812UK	187201	200 - 350 mm	25mm, 35mm, 47mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência
técnica

Europa

Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa

Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC

Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

