

Basic PDU, EB0809, 400 VAC, 3-PH, 32 A

CATALOGUSNUMMER

EB0809

Modular, compact PDU. Ultra-Low Profile Design

KENMERKEN

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUCTKENMERKEN

Productserie: Enlogic

Type: Basis-PDU

Producttype: Stekkerdoos

Type fitting: (18) C13; (6) C19

Aantal fittingen: 24

Kleur: Zwart

Stroomonderbreker: 16 A, 1-polig, Hy-Mag

Geschakelde stopcontacten: Nee

Aantal stroomonderbrekers: 6

Lengte ingangskabel: 3m

Locatie van de ingangskabel: Bovenste invoer

Ingangsspanning: 400V

Fase: 3 PH WYE

Onderbrekingsclassificatie: 5kAIC

Max. ingangsvermogen: 22.0 kVA

Stroomsterkte (verminderde stroomsterkte): 32 A

Uitgangsspanning: 200 – 240VAC

Rekeenheden: 0U

Stekkertype: IEC 60309 532P6 (IP44)

Type meting: Geen

Verwijderbare ingangskabel: Nee

Hoeveelheid in verpakking: 1

AANVULLENDE PRODUCTGEGEVENS

Please order bracket for vertical mounting separately.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE