

Panhead Screw, Torx with Grounding

Accessory parts like screws, washer and nuts enable the mounting of subrack components.



CERTIFICERINGEN



KENMERKEN

For fixing of subrack components

SPECIFICATIES

Productserie:	EuropacPRO
Type:	Panheadschroef
Producttype:	Schroef
Materiaal:	Staal
Afwerking:	Verzinkt

Table 1/1

Catalogusnummer	Lengte	Hoeveelheid in verpakking	Schroefdraadmaat	Werkt met	Aanhaalmoment	Snelle verzending
24560-151	6mm	100	M4	Subracks	1.3N·m	Nee
24560-155	10mm	100	M4	Subracks	2.4N·m	Nee

Catalogusnummer	Lengte	Hoeveelheid in verpakking	Schroefdraadm aat	Werkt met	Aanhaalmomen t	Snelle verzending
24560-131	14mm	10	M4	Subracks	2.4N·m	Nee
24560-130	14mm	100	M4	Subracks	2.4N·m	Nee

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE