

# Monitor, Keyboard, Touchpad, 1 U Drawer

## Data Solutions



Designed for standard 19" rackmount designed for comfort  
robust design for heavy use or harsh environment operation

### CERTIFICATIONS



### CARACTERÍSTICAS

Pull-out 17" TFT color monitor chassis, 1 U (resolution 1280 x 1024; connects to VGA interface)

Keyboard with different language keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 470 ... 740 mm

### ESPECIFICAÇÕES

**Profundidade:** 470mm

**Product Type:** Cabinet/Rack Drawer

Table 1/2

| Número de catálogo | Rack Height | Quantidade por embalagem | Cor | Código de cor | Tipo | Works With |
|--------------------|-------------|--------------------------|-----|---------------|------|------------|
|--------------------|-------------|--------------------------|-----|---------------|------|------------|

|           |    |   |           |          |                                   |              |
|-----------|----|---|-----------|----------|-----------------------------------|--------------|
| 60118-580 | 1U | 1 | Jet Black | RAL 9005 | Monitor,<br>Keyboard,<br>Touchpad | 19" Cabinets |
| 60118-581 | 1U | 1 | Jet Black | RAL 9005 | Monitor,<br>Keyboard,<br>Touchpad | 19" Cabinets |
| 60118-582 | 1U | 1 | Jet Black | RAL 9005 | Monitor,<br>Keyboard,<br>Touchpad | 19" Cabinets |

Table 2/2

| Número de catálogo | Keyboard Type |
|--------------------|---------------|
| 60118-580          | QWERTY UK     |
| 60118-581          | QWERTZ        |
| 60118-582          | AZERTY        |

## DETALHES ADICIONAIS DO PRODUTO

Further versions on request. With trackball or numeric pad.

Other Keyboard layouts see user manual.

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**