

## Shelf for air circuit-breakers (ACB) | Distribuição de energia, MSCC



The galvanised steel shelf, MSCC, covers a partial depth of an enclosure and is ideal for equipment requiring strong fixation, such as heavy air circuit brakers. It leaves the rear of the enclosure accessible for easy installation and wiring.

## CARACTERISTICAS

Descrição: Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette. The shelf has ventilation slots to allow air circulation in the section. It can be mounted only if we have internal side panels MSPSxx06 in both sides. Adjustable height position in steps of 25mm. It can not be used with the front covers system, if it is neccessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections.

Material: 2 mm galvanised steel.

Fornecimento: 1 piece with mounting material.

In order to mount the shelf, internal side panels (MSPS), are required

Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette

The shelf has ventilation slots to allow air circulation in the section

It can be mounted only if we have internal side panels MSPSxx06 in both sides

Adjustable height position in steps of 25mm

d with the front covers system, if it is neccessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections it can not be use

Includes mounting hardware

## **ESPECIFICAÇÕES**

**Espessura**: 2mm

Material: Aço Macio
Acabamento: Plated

Table 1/1						
Número de catálogo	Altura	Largura	Profundidade	Largura da placa de montagem	Profundidade máxima de montagem	Material do gabinete
MSCC1006	78mm	1000mm	600mm	904mm	283mm	Aço Macio
MSCC0606	78mm	600mm	600mm	504mm	283mm	Aço Macio
MSCC0806	78mm	800mm	600mm	704mm	283mm	Aço Macio

## **AVISO**

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE