


EuropacPRO Rear Hood for Stainless Steel EMC Gasket

Power Utilities



The rear hood is used as a shielded rear boundary and requires 60 mm space. Therefore if the rear hood is used, the side panel depth must be 60 mm greater than the board depth. Contact between the rear hood and the horizontal rails is established by the stainless steel contact strip for the cover plate. Thus no additional EMC sealing is necessary. Rear hood cannot be used simultaneously with rear corner profile.

CERTIFICERINGEN



KENMERKEN

The rear hood is used as a shielded rear boundary. The rear hood requires 60 mm space. Therefore if the rear hood is used, the side panel depth must be 60 mm greater than the board depth. Example: For a board depth of 160 mm a side panel (with rear hood) of 235 mm (175 mm + 60 mm) is used

Contact between the rear hood and the horizontal rails is established by the stainless steel contact strip for the cover plate. Thus no additional EMC sealing is necessary

Rear hood cannot be used simultaneously with rear corner profile

For EMC-shielding please order EMC gasket for horizontal rail separately.

SPECIFICATIES

Table 1/2

Catalogusnummer	Rekhoogte	Rekbreedte	Pakkethoeveelheid	Productfamilie	Producttype	Type
34561-763	6 U	63 HP	1	EuropacPRO	Dekking	Achterkap

Catalogusnummer	Rekhoogte	Rekbreedte	Pakkethoeveelheid	Productfamilie	Producttype	Type
34561-752	3 U	84 HP	1	EuropacPRO	Dekking	Achterkap
34561-750	3 U	42 HP	1	EuropacPRO	Dekking	Achterkap
34561-764	6 U	84 HP	1	EuropacPRO	Dekking	Achterkap

Table 2/2

Catalogusnummer	Werkt met
34561-763	Subracks
34561-752	Subracks
34561-750	Subracks
34561-764	Subracks

AANVULLENDE PRODUCTGEGEVENS

Required quantity of screws per rear hood: 3 U subrack 10 screws; 6 U subrack 16 screws.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE