


Front Handle One-Piece, Width 12,2 mm

Energiebedrijven



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFICERINGEN



KENMERKEN

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Package Quantity	Handle Type	Kleur	Materiaal	Product Family
10501-116	1 U	1	Recht	Silver	Aluminium	EuropacPRO
10501-004	2 U	1	Recht	Silver	Aluminium	EuropacPRO
10501-020	3 U	1	Angled Handle	Silver	Aluminium	EuropacPRO

Catalogusnummer	Rack Height	Package Quantity	Handle Type	Kleur	Materiaal	Product Family
10501-026	3 U	1	Recht	Zwart	Aluminium	EuropacPRO
10501-005	3 U	1	Recht	Silver	Aluminium	EuropacPRO
10501-006	4 U	1	Recht	Silver	Aluminium	EuropacPRO
10501-007	5 U	1	Recht	Silver	Aluminium	EuropacPRO
10501-022	6 U	1	Angled Handle	Silver	Aluminium	EuropacPRO
10501-029	6 U	1	Recht	Zwart	Aluminium	EuropacPRO
10501-008	6 U	1	Recht	Silver	Aluminium	EuropacPRO
10501-016	2 U	1	Recht	Silver	Aluminium	EuropacPRO
10501-021	4 U	1	Angled Handle	Silver	Aluminium	EuropacPRO
10501-018	4 U	1	Recht	Silver	Aluminium	EuropacPRO
10501-025	2 U	1	Recht	Zwart	Aluminium	EuropacPRO
10501-027	4 U	1	Recht	Zwart	Aluminium	EuropacPRO
10501-028	5 U	1	Recht	Zwart	Aluminium	EuropacPRO

Table 2/2

Catalogusnummer	Product Type	Works With	Aandraaimoment
10501-116	Handle	Subracks	
10501-004	Handle	Subracks	
10501-020	Handle	Subracks	2.4 N·m
10501-026	Handle	Subracks	2.4 N·m

Catalogusnummer	Product Type	Works With	Aandraaimoment
10501-005	Handle	Subracks	2.4 N·m
10501-006	Handle	Subracks	
10501-007	Handle	Subracks	
10501-022	Handle	Subracks	2.4 N·m
10501-029	Handle	Subracks	2.4 N·m
10501-008	Handle	Subracks	2.4 N·m
10501-016	Handle	Subracks	
10501-021	Handle	Subracks	2.4 N·m
10501-018	Handle	Subracks	2.4 N·m
10501-025	Handle	Subracks	
10501-027	Handle	Subracks	
10501-028	Handle	Subracks	

ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE