


Front Panel EMC Textile Shielding Kit, -40 up to +85°C

Energiebedrijven



The textile EMC gaskets are inserted into a slot on the right hand side of the U-shaped front panels. The gaskets are glued to the front panel. For an expanded temperature range up to +85°C.

CERTIFICERINGEN



KENMERKEN

Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.

Profile seal is bonded onto the contact surface of the 19" bracket or of the rear angle and sets up the conductive connection to the U-shaped front panels

Temperature range -40 °C ... +85 °C

SPECIFICATIES

Table 1/1

Catalogusnummer	Rack Height	Package Quantity	Product Family	Product Type	Works With
-----------------	-------------	------------------	----------------	--------------	------------

21102-857	2 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-853	3 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-854	3 U	100	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-858	4 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-978	5 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-855	6 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-856	6 U	100	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-859	9 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels

ADDITIONAL PRODUCT DETAILS

EMC gaskets (textile) are required for shielding the front panels.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE