

Front Panel, Unshielded, With Fastener Pin

Energiebedrijven



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

CERTIFICERINGEN



KENMERKEN

Enable grounding of the front area (protection class 1)

SPECIFICATIES

Table 1/3						
Catalogusnummer	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish	Treated Edges
20119-159	7 HP	1	Screw-on Front	Anodized	Conductive	Nee
20119-160	14 HP	1	Screw-on Front	Anodized	Conductive	Nee
20119-161	21 HP	1	Screw-on Front	Anodized	Conductive	Nee
20119-162	28 HP	1	Screw-on Front	Anodized	Conductive	Nee

Catalogusnummer	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish	Treated Edges
20119-163	42 HP	1	Screw-on Front	Anodized	Anodized	Nee

Table 2/3

Catalogusnummer	Voltoet aan	EMC Shielding	Hoogte	Materiaal	Product Type	Rack Height
20119-159	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium	Front Panel	3 U
20119-160	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium	Front Panel	3 U
20119-161	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium	Front Panel	3 U
20119-162	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium	Front Panel	3 U
20119-163	IEC 60297-3-101, IEEE 1101.1/10	Nee	128.4 mm	Aluminium	Front Panel	3 U

Table 3/3

Catalogusnummer	Type	Breedte
20119-159	Front Panel without Handle	35.2 mm
20119-160	Front Panel without Handle	70.8 mm
20119-161	Front Panel without Handle	106.3 mm
20119-162	Front Panel without Handle	141.9 mm
20119-163	Front Panel without Handle	213 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte