

Guide Rail With Coding, preassembled ESD Clip for CompactPCI/ VME64x, PC

Power Utilities

KENMERKEN

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to an optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

ESD clip for an conductive contact between PCB and horizontal rail preassembled

Storage temperature: from -40 °C ... 130 °C

SPECIFICATIES

Table 1/2						
Catalogusnummer	Kleur	Pakkethoeveelheid	Diepte van de plank	Groefbreedte	Voldoet aan	Materiaal
24568-847	Rood	10	160 mm	2	EN 45545-2	Polycarbonaat
24568-848	Grijs	10	160 mm	2	EN 45545-2	Polycarbonaat
24568-850	Rood	10	160 mm	2	EN 45545-2	Polycarbonaat
24568-851	Grijs	10	160 mm	2	EN 45545-2	Polycarbonaat
24568-853	Rood	10	70 mm	2	EN 45545-2	Polycarbonaat

Catalogusnummer	Kleur	Pakkethoeveelheid	Diepte van de plank	Groefbreedte	Voldoet aan	Materiaal
24568-854	Grijs	10	70 mm	2	EN 45545-2	Polycarbonaat
24568-855	Rood	10	70 mm	2	EN 45545-2	Polycarbonaat
24568-856	Grijs	10	70 mm	2	EN 45545-2	Polycarbonaat

Table 2/2				
Catalogusnummer	Productfamilie	Producttype	Type	Werkt met
24568-847	EuropacPRO, RatiopacPRO, RatiopacPRO LUCHT, CompacPRO, PropacPRO, MultipacPRO, Inpac	Geleiderail	With Coding and preassembled ESD Clips	Subracks, Gevallen, 19- inch chassis, Systemen
24568-848	EuropacPRO, RatiopacPRO, RatiopacPRO LUCHT, CompacPRO, PropacPRO, MultipacPRO, Inpac	Geleiderail	With Coding and preassembled ESD Clips	Subracks, Gevallen, 19- inch chassis, Systemen
24568-850	EuropacPRO, RatiopacPRO, RatiopacPRO LUCHT, CompacPRO, PropacPRO, MultipacPRO, Inpac	Geleiderail	With Coding and preassembled ESD Clips	Subracks, Gevallen, 19- inch chassis, Systemen
24568-851	EuropacPRO, RatiopacPRO, RatiopacPRO LUCHT, CompacPRO, PropacPRO, MultipacPRO, Inpac	Geleiderail	With Coding and preassembled ESD Clips	Subracks, Gevallen, 19- inch chassis, Systemen
24568-853	EuropacPRO, RatiopacPRO, RatiopacPRO LUCHT, CompacPRO, PropacPRO, MultipacPRO, Inpac	Geleiderail	With Coding and preassembled ESD Clips	Subracks, Gevallen, 19- inch chassis, Systemen
24568-854	EuropacPRO, RatiopacPRO, RatiopacPRO LUCHT, CompacPRO, PropacPRO, MultipacPRO, Inpac	Geleiderail	With Coding and preassembled ESD Clips	Subracks, Gevallen, 19- inch chassis, Systemen

Catalogusnummer	Productfamilie	Producttype	Type	Werkt met
24568-855	EuropacPRO, RatiopacPRO, RatiopacPRO LUCHT, CompacPRO, PropacPRO, MultipacPRO, Inpac	Geleiderail	With Coding and preassembled ESD Clips	Subracks, Gevallen, 19- inch chassis, Systemen
24568-856	EuropacPRO, RatiopacPRO, RatiopacPRO LUCHT, CompacPRO, PropacPRO, MultipacPRO, Inpac	Geleiderail	With Coding and preassembled ESD Clips	Subracks, Gevallen, 19- inch chassis, Systemen

AANVULLENDE PRODUCTGEGEVENS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE