

Outdoor Modular VENT Cabinet

Energiebedrijven



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

CERTIFICERINGEN



KENMERKEN

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from all sides

SPECIFICATIES

Table 1/2

Catalogusnummer	Product Type	Product Family	Rack Height	Hoogte	Breedte	Diepte
10149-334	Outdoor Cabinet	Modulair	29 U	1530 mm	700 mm	730 mm
10149-336	Outdoor Cabinet	Modulair	29 U	1530 mm	1300 mm	630 mm

Catalogusnummer	Product Type	Product Family	Rack Height	Hoogte	Breedte	Diepte
10149-337	Outdoor Cabinet	Modulair	29 U	1530 mm	1300 mm	630 mm

Table 2/2

Catalogusnummer	Wall Type	Door Type	Access	Koelsystemen	EMC Shielding	Voldoet aan
10149-334	Double Walled	Single Door	Front	Fan Ventilation	No (Retrofittable)	IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4
10149-336	Double Walled	Double Door	Front	Fan Ventilation	No (Retrofittable)	IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4, RC2
10149-337	Double Walled	Double Door	Front	Fan Ventilation	No (Retrofittable)	IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4

ADDITIONAL PRODUCT DETAILS

Height dimensions are without base/plinth.

qW = specific heat dissipation capacity according to ETSI EN 300 019-1-4.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE