

Guide Rail With Coding, preassembled ESD Clip for CompactPCI/ VME64x, PC

Concessionárias de energia

RECURSOS

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to an optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

ESD clip for an conductive contact between PCB and horizontal rail preassembled

Storage temperature: from -40 °C ... 130 °C

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Cor	Package Quantity	Board Depth	Groove Width	Em conformidade com	Material
24568-847	Vermelho	10	160 mm	2	EN 45545-2	Policarbonato
24568-848	Grey	10	160 mm	2	EN 45545-2	Policarbonato
24568-850	Vermelho	10	160 mm	2	EN 45545-2	Policarbonato
24568-851	Grey	10	160 mm	2	EN 45545-2	Policarbonato
24568-853	Vermelho	10	70 mm	2	EN 45545-2	Policarbonato

Número do catálogo	Cor	Package Quantity	Board Depth	Groove Width	Em conformidade com	Material
24568-854	Grey	10	70 mm	2	EN 45545-2	Polycarbonato
24568-855	Vermelho	10	70 mm	2	EN 45545-2	Polycarbonato
24568-856	Grey	10	70 mm	2	EN 45545-2	Polycarbonato

Table 2/2				
Número do catálogo	Product Family	Product Type	Tipo	Works With
24568-847	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-848	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-850	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-851	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-853	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems

Número do catálogo	Product Family	Product Type	Tipo	Works With
24568-854	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-855	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-856	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE