

Varistar CP Steel Door, Plain With Multi-Point Locking, Shortened

Energiebedrijven

EMC and IP55 Steel Door with lever handle and 5-Point locking.

KENMERKEN

Height of connection plate 400 mm

Lever handle with push button

Opening angle 180°

Steel door with 5-point locking for EMC applications

SPECIFICATIES

Table 1/2

Catalogusnummer	Rack Height	Hoogte	Breedte	Protection Rating	Kleur	Color Code
21630-372	38 U	1800 mm	600 mm	IP55	Black Grey	RAL 7021
21630-373	38 U	1800 mm	800 mm	IP55	Black Grey	RAL 7021
21630-711	38 U	1800 mm	600 mm	IP55	Black Grey	RAL 7021
21630-712	38 U	1800 mm	800 mm	IP55	Black Grey	RAL 7021
21630-374	42 U	2000 mm	600 mm	IP55	Black Grey	RAL 7021
21630-375	42 U	2000 mm	800 mm	IP55	Black Grey	RAL 7021
21630-376	47 U	2200 mm	600 mm	IP55	Black Grey	RAL 7021

Catalogusnummer	Rack Height	Hoogte	Breedte	Protection Rating	Kleur	Color Code
21630-377	47 U	2200 mm	800 mm	IP55	Black Grey	RAL 7021
21630-713	42 U	2000 mm	600 mm	IP55	Black Grey	RAL 7021
21630-714	42 U	2000 mm	800 mm	IP55	Black Grey	RAL 7021
21630-715	47 U	2200 mm	600 mm	IP55	Black Grey	RAL 7021
21630-716	47 U	2200 mm	800 mm	IP55	Black Grey	RAL 7021

Table 2/2

Catalogusnummer	Locking Type	Product Type
21630-372	3-Point Locking	Cabinet Door
21630-373	3-Point Locking	Cabinet Door
21630-711	3-Point Locking	Cabinet Door
21630-712	3-Point Locking	Cabinet Door
21630-374	4-Point Locking	Cabinet Door
21630-375	4-Point Locking	Cabinet Door
21630-376	4-Point Locking	Cabinet Door
21630-377	4-Point Locking	Cabinet Door
21630-713	4-Point Locking	Cabinet Door
21630-714	4-Point Locking	Cabinet Door
21630-715	4-Point Locking	Cabinet Door
21630-716	4-Point Locking	Cabinet Door

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE