

Connection Kit, Cold Applied, for PI Heaters, ATEX



nVent RAYCHEM CS-150-xx-PI are a range of low profile, under-insulation power connection or splice for polymer insulated (PI) series heating cables, using two component silicone compound to provide durable and flexible moisture proof encapsulation. Available in 3 versions, to allow robust & reliable connections up to 125A and approved for use in hazardous area. The internal electrical connection is by nickel plated crimps, specifically designed to provide reliable electrical connections over a very wide temperature range.

KENMERKEN

Simple and fast to install

Cold applied: no heat gun, no hot work permit needed

Low profile, under-insulation component

Unique design, to ensure optimum connection reliability

Approved for use in hazardous areas

SPECIFICATIES

Max Operating Temperature:	200 °C
Aansluiting type:	Cold Applied
Area Classification:	Non-Hazardous; Hazardous
IP-classificatie:	IP65
Voltage Rating:	Max. 750 V

Table 1/1

Catalogusnummer	Naam van het item	Current Rating	Suitable for Cold Lead
1244-000588	CS-150-6-PI	54 A	4 – 6 mm ²
1244-000587	CS-150-25-PI	129 A	10 – 25 mm ²
1244-000586	CS-150-2.5-PI	32 A	0 – 2.5 mm ²

ADDITIONAL PRODUCT DETAILS

Attribute Current Rating is applicable when used as hot-cold joint.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT