


E650C-R Gutter Sensor for Elexant 650c-Modbus



Rod-shaped sensor E650C-R for combined measurement of temperature and moisture values in gutters and neighbouring areas, such as flat roofs and downpipes to be used with Elexant 650c-Modbus. Robust version made of brass, fully encapsulated. Extremely compact design with axial cable outlet and threaded bolt for fixing in position. Optional mounting plate for sensor E650C-R can be used with sensor height adjustment above the mounting surface. The mounting plate can be matched to the mounting location by bending and then attached by gluing or soldering. Two material versions are available for suitable material combinations in gutter and flat roof applications.

KENMERKEN

Cable connection: Axial

Connection cable: 4 x 0.5 mm²

Temperature range for moisture measurement: -20°C to 30°C

SPECIFICATIES

Table 1/2

Catalogusnummer	Artikelnaam	Communicatie	Diepte	Gevaarlijke omgeving	Hoogte	IP-classificatie
1244-022799	E650C-R-BRACKET-CU	Nee	80 mm	Nee	2 mm	IP68
1244-022798	E650C-R-BRACKET-ZN	Nee	80 mm	Nee	2 mm	IP68
1244-022795	E650C-R	Nee	96 mm	Nee	14 mm	IP68

Table 2/2

Catalogusnummer	Artikelnaam	Meetbereik	Breedte
1244-022799	E650C-R-BRACKET-CU		132 mm

Catalogusnummer	Artikelnaam	Meetbereik	Breedte
1244-022798	E650C-R-BRACKET-ZN		132 mm
1244-022795	E650C-R	-20 to 30 °C	14 mm

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Ons krachtige merkenportfolio:

RAYCHEM PYROTENAX TRACER NUHEAT