

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

Concessionárias de energia

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

RECURSOS

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

ESPECIFICAÇÕES

Table 1/3

Número do catálogo	Rack Height	Altura	Frame Color	Largura	Frame Color Code	Cladding Material
10630-034	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Aço
10630-033	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Aço
10630-035	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Aço
10630-036	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Aço

Table 2/3

Número do catálogo	Profundidade	Cladding Color	Cladding Color Code	Em conformidade com	Frame Material	Product Type
10630-034	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Aço	Cabinet
10630-033	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Aço	Cabinet
10630-035	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Aço	Cabinet
10630-036	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Aço	Cabinet

Table 3/3

Número do catálogo	Carga estática
10630-034	400 kgf
10630-033	400 kgf
10630-035	400 kgf
10630-036	400 kgf

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE