

HWAT-T55 Thermostat



nVent RAYCHEM HWAT-T55 is an energy efficient thermostat for use in nVent RAYCHEM HWAT self-regulating single pipe hot water systems, in small pipe networks or for branch lines.

KENMERKEN

Simple to install and operate: digital display for temperature and alarm, 35 mm DIN-Rail mountable

Energy saving: 3 operating modes ON/ECO/OFF; with HWAT-L the system can be switched ON/OFF during absence periods, with HWAT-M/R there are three preset temperatures 55/50/45 °C, integrated clock and energy savings (ECO) for off-peak usage

System monitoring through high temperature alarm: if a temperature over 66 °C is measured the system will be switched off to avoid scalding and calcification

System monitoring through low temperature alarm: to avoid unnecessary energy consumption when hot water storage problems occur

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIES

Table 1/2

Catalogusnummer	Naam van het item	IP-classificatie	Voltage Rating	Voltage Rating Type	Adjustment Range	Nominal Switching Current @ 250V, Potential Free
1244-015722	HWAT-T55	IP20	195 – 253 V	AC	40 – 60 °C	16 A

Table 2/2

Catalogusnummer	Naam van het item	Power Consumption, Standby	Hoogte	Breedte	Diepte

1244-015722	HWAT-T55	5 W	87.5 mm	52.5 mm	87.5 mm
-------------	----------	-----	---------	---------	---------

ADDITIONAL PRODUCT DETAILS

The nVent RAYCHEM HWAT-T55 thermostat is designed for use with HWAT-L, -M or -R. Maximum circuit length is limited to 50 m. For temperature adjustment, consider local hygienic standards.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

Noord-Amerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latijns-Amerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT