

Varistar CP Steel Door, Plain With 3-Point Locking, IP55

Concessionárias de energia

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

RECURSOS

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

ESPECIFICAÇÕES

Table 1/3

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Em conformidade com
21630-171	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-210	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-211	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-212	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-213	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-214	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-215	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Em conformidade com
21630-216	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-217	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-218	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-219	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-220	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Número do catálogo	Acabamento	Locking Type	Material	Product Type	Protection Rating	Tipo
21630-171	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-210	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-211	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-212	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-213	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-214	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-215	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-216	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-217	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-218	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door
21630-219	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door

Número do catálogo	Acabamento	Locking Type	Material	Product Type	Protection Rating	Tipo
21630-220	Powder Coated	3-Point Locking	Aço	Cabinet Door	IP55	Steel Door

Table 3/3

Número do catálogo	Works With
21630-171	Varistar CP
21630-210	Varistar CP
21630-211	Varistar CP
21630-212	Varistar CP
21630-213	Varistar CP
21630-214	Varistar CP
21630-215	Varistar CP
21630-216	Varistar CP
21630-217	Varistar CP
21630-218	Varistar CP
21630-219	Varistar CP
21630-220	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE