

Varistar CP Swing Frame for 800 mm Width

Concessionárias de energia

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

RECURSOS

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Rack Height	Cor	Color Code	Altura	Material	Product Type
21630-669	24 U	Black Grey	RAL 7021	1200 mm	Aço	Cabinet/Rack Frame
21630-680	24 U	Black Grey	RAL 7021	1200 mm	Aço	Cabinet/Rack Frame
21630-671	29 U	Black Grey	RAL 7021	1400 mm	Aço	Cabinet/Rack Frame
21630-681	29 U	Black Grey	RAL 7021	1400 mm	Aço	Cabinet/Rack Frame
21630-673	33 U	Black Grey	RAL 7021	1600 mm	Aço	Cabinet/Rack Frame
21630-682	33 U	Black Grey	RAL 7021	1600 mm	Aço	Cabinet/Rack Frame
21630-675	38 U	Black Grey	RAL 7021	1800 mm	Aço	Cabinet/Rack Frame

Número do catálogo	Rack Height	Cor	Color Code	Altura	Material	Product Type
21630-683	38 U	Black Grey	RAL 7021	1800 mm	Aço	Cabinet/Rack Frame
21630-677	42 U	Black Grey	RAL 7021	2000 mm	Aço	Cabinet/Rack Frame
21630-684	42 U	Black Grey	RAL 7021	2000 mm	Aço	Cabinet/Rack Frame
21630-679	47 U	Black Grey	RAL 7021	2200 mm	Aço	Cabinet/Rack Frame
21630-685	47 U	Black Grey	RAL 7021	2200 mm	Aço	Cabinet/Rack Frame

Table 2/2

Número do catálogo	Protection Rating	Largura
21630-669	IP20	800 mm
21630-680	IP20	800 mm
21630-671	IP20	800 mm
21630-681	IP20	800 mm
21630-673	IP20	800 mm
21630-682	IP20	800 mm
21630-675	IP20	800 mm
21630-683	IP20	800 mm
21630-677	IP20	800 mm
21630-684	IP20	800 mm
21630-679	IP20	800 mm
21630-685	IP20	800 mm

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE