

# NGC-40 Series, Control Module



The nVent RAYCHEM NGC-40-HTC (for single-phase heaters) and NGC-40-HTC3 (for three-phase heaters) modules are used to control either a solid-state relay or contactor within the NGC-40 control and monitoring system. This module also has one alarm output and one digital input. The alarm output can be used to control an external annunciator. The digital input is programmable and may be used for various functions such as forcing outputs on and off. Other features of this module include ground-fault and line current sensing for both HTC and HTC3. The front panel of the HTC module has LED indicators for various status conditions. The front panel also provides a ground-fault and heater test button.

## KENMERKEN

Din-rail mounted and part of the NGC-40 system

Individual single circuit control provides highest reliability for critical heat tracing circuits

Maximum design flexibility, by using the innovative data sharing among the heat tracing circuits within a panel, as well as, the programmable digital inputs and alarm outputs of each control module

Permanent supervision of the integrity of the heat tracing circuit and detailed problem reporting simplifies maintenance and increases personnel safety

## SPECIFICATIES

|                             |               |
|-----------------------------|---------------|
| <b>Voltage Rating:</b>      | 24 V          |
| <b>Voltage Rating Type:</b> | DC            |
| <b>Bedrijfstemperatuur:</b> | -40 tot 65 °C |

Table 1/1

| Catalogusnummer | Naam van het item | Heat-Tracing Circuit |
|-----------------|-------------------|----------------------|
| 10730-004       | NGC-40-HTC3       | Three-Phase          |

| Catalogusnummer | Naam van het item | Heat-Tracing Circuit |
|-----------------|-------------------|----------------------|
| 10730-003       | NGC-40-HTC        | Single-Phase         |

## WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van [www.nvent.com](http://www.nvent.com) of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.

### Noord-Amerika

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latijns-Amerika

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**