

Modular Jumper Cable, Metal Connectors

nVent RAYCHEM TraceTek TT-MJC-XX is a range of jumper cables, with metal connectors, available in various fixed lengths.

RECURSOS

Simple and fast to install, modular

Easy to design

ESPECIFICAÇÕES

Core Quantity:	4
Diâmetro externo:	4,2 mm
Tamanho do condutor:	18 AWG
Core Identification:	Cor
Conductor Material:	Cobre
Outer Sheath Material:	ECTFE
Insulation Material:	Fluorinated Ethylene Propylene (FEP)
Connector Material:	Metal

Table 1/1

Número do catálogo	Nome do item	Comprimento	Cor
013247-000	TT-MJC-1M/3FT-MC	1 m	Clear Jacket
057111-000	TT-MJC-15M/50FT-MC	15 m	Clear Jacket
078783-000	TT-MJC-3M/10FT-MC	3 m	Clear Jacket
169643-000	TT-MJC-7.5M/25FT-MC	7.5 m	Clear Jacket
935637-000	TT-MJC-30M/100FT-MC	30 m	Clear Jacket
664356-000	TT-MJC-30M/100FT-MC-BLK	30 m	Preto
678452-000	TT-MJC-15M/50FT-MC-BLK	15 m	Preto

Número do catálogo	Nome do item	Comprimento	Cor
693994-000	TT-MJC-7.5M/25FT-MC-BLK	7.5 m	Preto
709898-000	TT-MJC-3M/10FT-MC-BLK	3 m	Preto
726164-000	TT-MJC-1M/3FT-MC-BLK	1 m	Preto

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT