

TT-TS12 Alarm Panel



nVent RAYCHEM TraceTek TT-TS12 Touch Screen Panel provides a graphic user interface to manage and display information from a network of up to 250 external leak detection circuits. With interactive and dynamic leak location maps and displays, the leak location can be displayed on the floor plan, piping layout or photo of a single piece of equipment. Provides a quick status overview of all leak detection cables. Works with TTSIM or wireless mesh transmitters.

RECURSOS

Easy to install, simple to set up and operate

Graphic display of leak location: 12" full color, high resolution SVGA touch screen display

Flexible interface options: audible alarm, summary relays, serial data and web interfaces are provided as standard

Onboard memory for up to 5000 events, simple off-line archiving and software updates

Available in various configurations

Email alerts allow 24/7 remote notification of an alarm

CE and UL 508 compliant

ESPECIFICAÇÕES

Relay Contacts:	8 Relays (4 System, 4 User Programmable)
Display:	12" Touch Screen, TFT LCD
Profundidade:	210 mm
Altura:	400 mm
Largura:	500 mm
Operating Temperature:	-20 a 60 °C

Table 1/1

Número do catálogo	Nome do item	Number of TTSIM
1244-015332	TT-TS12-E-PANEL-S1-1	1 x TTSIM-1
1244-015336	TT-TS12-E-PANEL-S1A-1	1 x TTSIM-1A

Número do catálogo	Nome do item	Number of TTSIM
1244-015333	TT-TS12-E-PANEL-S1-2	2 x TTSIM-1
1244-015337	TT-TS12-E-PANEL-S1A-2	2 x TTSIM-1A
1244-015334	TT-TS12-E-PANEL-S1-3	3 x TTSIM-1
1244-015338	TT-TS12-E-PANEL-S1A-3	3 x TTSIM-1A
1244-015335	TT-TS12-E-PANEL-S1-4	4 x TTSIM-1
1244-015339	TT-TS12-E-PANEL-S1A-4	4 x TTSIM-1A
1244-015331	TT-TS12-E-PANEL-0	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT