

nVent ERIFLEX Flexbus IP55 lederoppføring

Data Solutions



nVent ERIFLEX Flexbus IP55 Conductor Entries can be used for switchboard and/or power supply cover to upgrade an installation to IP55 level. Protect the nVent ERIFLEX Flexbus Conductor insulation against sharp edges from power supply or switchboard top cover.

SERTIFISERINGER



FUNKSJONER

I samsvar med RoHS

Made with soft PVC to follow any potential conductor bending radius

Sealing around the conductor is made by a self-fusing tape with a strong adhesive

Good resistance to solvent and hydrocarbon splashes

Adaptable to any nVent ERIFLEX Flexbus conductor cross section by cutting the top material with traditional cutter

High acid resistance

UV resistance

Flame retardant

SPESIFIKASJONER

Merkeverdi:	IP 55
Materiale:	Polyvinylklorid
Arbeidstemperatur:	-40 to 140°C


Table 1/2

Katalognummer	Artikkelnummer	Type	A	B.	C.	Sjåførens størrelse
FLEXCEIP55C501	508140	Entry	126mm	102mm	175mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²
FLEXCEIP55C1001	508141	Entry	176mm	102mm	152mm	960 mm ² , 1280 mm ² , 1810 mm ²
FLEXCEIP55C502	508142	Dobbel inngang	126mm	157mm	175mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²
FLEXCEIP55C1002	508143	Dobbel inngang	176mm	157mm	152mm	960 mm ² , 1280 mm ² , 1810 mm ²

Table 2/2

Katalognummer	Artikkelnummer	Tiltrekkingsmoment (TQ)	Vekt på enhet
FLEXCEIP55C501	508140	2.5N·m	0.6kg
FLEXCEIP55C1001	508141	2.5N·m	0.7kg
FLEXCEIP55C502	508142	2.5N·m	0.8kg
FLEXCEIP55C1002	508143	2.5N·m	1kg

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE