

## CleanTray 45-graders albue



Clean Tray 45-Degree Elbows are used for continuous runs with 45-degree turns. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

### FUNKSJONER

---

Clean Tray 45-Degree Elbows are used for continuous runs with 45-degree turns

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

## SPESIFIKASJONER

**Avslutt:** Innlegg #3

**Materiale:** Rustfritt stål 304

Table 1/1

| Katalognummer | Type  | Høyde | Bredde | Tykkelse | Hurtiglevering |
|---------------|-------|-------|--------|----------|----------------|
| CT22EFC45SS   | Albue | 51mm  | 51mm   | 1.27mm   | Nei            |
| CT33EFC45SS   | Albue | 76mm  | 76mm   | 1.27mm   | Nei            |
| CT33EIC45SS   | Albue | 76mm  | 76mm   | 1.27mm   | Nei            |
| CT33EOC45SS   | Albue | 76mm  | 76mm   | 1.27mm   | Nei            |
| CT44EFC45SS   | Albue | 102mm | 102mm  | 1.27mm   | Nei            |
| CT44EIC45SS   | Albue | 102mm | 102mm  | 1.27mm   | Nei            |
| CT44EOC45SS   | Albue | 102mm | 102mm  | 1.27mm   | Nei            |
| CT44PEFC45SS  | Albue | 102mm | 102mm  | 1.27mm   | Nei            |
| CT46EFC45SS   | Albue | 102mm | 152mm  | 1.27mm   | Nei            |
| CT46EIC45SS   | Albue | 102mm | 152mm  | 1.27mm   | Nei            |
| CT46EOC45SS   | Albue | 102mm | 152mm  | 1.27mm   | Nei            |
| CT66EFC45SS   | Albue | 152mm | 152mm  | 1.27mm   | Nei            |
| CT66EOC45SS   | Albue | 152mm | 152mm  | 1.27mm   | Nei            |
| CTS33EFC45SS  | Albue | 76mm  | 76mm   | 1.27mm   | Nei            |
| CTS33PEFC45SS | Albue | 76mm  | 76mm   | 1.27mm   | Nei            |
| CTS44EFC45SS  | Albue | 102mm | 102mm  | 1.27mm   | Nei            |
| CTS44PEFC45SS | Albue | 102mm | 102mm  | 1.27mm   | Nei            |

| Katalognummer | Type  | Høyde | Bredde | Tykkelse | Hurtiglevering |
|---------------|-------|-------|--------|----------|----------------|
| CTS46EFC45SS  | Albue | 102mm | 152mm  | 1.27mm   | Nei            |
| CTS46PEFC45SS | Albue | 102mm | 152mm  | 1.27mm   | Nei            |
| CTS66EFC45SS  | Albue | 152mm | 152mm  | 1.27mm   | Nei            |
| CTS66PEFC45SS | Albue | 152mm | 152mm  | 1.27mm   | Nei            |
| CT22EIC45SS   | Albue | 51mm  | 51mm   | 1.27mm   | Nei            |
| CT22EOC45SS   | Albue | 51mm  | 51mm   | 1.27mm   | Nei            |
| CT22PEFC45SS  | Albue | 51mm  | 51mm   | 1.27mm   | Nei            |
| CT33PEFC45SS  | Albue | 76mm  | 76mm   | 1.27mm   | Nei            |
| CT46PEFC45SS  | Albue | 102mm | 152mm  | 1.27mm   | Nei            |
| CT66EIC45SS   | Albue | 152mm | 152mm  | 1.27mm   | Nei            |
| CT66PEFC45SS  | Albue | 152mm | 152mm  | 1.27mm   | Nei            |

## ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på [www.nvent.com](http://www.nvent.com) og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**