

Hylle for Air Circuit-Breakers (ACB) for kraftdistribusjon, MSCC



The galvanised steel shelf, MSCC, covers a partial depth of an enclosure and is ideal for equipment requiring strong fixation, such as heavy air circuit breakers. It leaves the rear of the enclosure accessible for easy installation and wiring.

FUNKSJONER

Beskrivelse: Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette. The shelf has ventilation slots to allow air circulation in the section. It can be mounted only if we have internal side panels MSPSxx06 in both sides. Adjustable height position in steps of 25mm. It can not be used with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections.

Materiale: 2 mm galvanised steel.

Levering: 1 piece with mounting material.

Inkluderer festemidler

In order to mount the shelf, internal side panels (MSPS), are required

Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette

The shelf has ventilation slots to allow air circulation in the section

It can be mounted only if we have internal side panels MSPSxx06 in both sides

Adjustable height position in steps of 25mm

d with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections it can not be use

Includes mounting hardware

SPESIFIKASJONER

- Tykkelse:

2mm
- Materiale:

Mild stål
- Avslutt:

Belagt

Table 1/1						
Katalognummer	Høyde	Bredde	Dybde	Bredde på monteringsplate	Maks. Monteringsdybde	Innkapslingsmateriale
MSCC1006	78mm	1000mm	600mm	904mm	283mm	Mild stål
MSCC0606	78mm	600mm	600mm	504mm	283mm	Mild stål
MSCC0806	78mm	800mm	600mm	704mm	283mm	Mild stål

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE