


Front Panel EMC Textile Shielding Kit, -40 up to +85°C

Strømforsyning



The textile EMC gaskets are inserted into a slot on the right hand side of the U-shaped front panels. The gaskets are glued to the front panel. For an expanded temperature range up to +85°C.

SERTIFISERINGER



FUNKSJONER

Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.

Profile seal is bonded onto the contact surface of the 19" bracket or of the rear angle and sets up the conductive connection to the U-shaped front panels

Temperature range -40 °C ... +85 °C

SPESIFIKASJONER

Table 1/1

Katalognummer	Rack Height	Package Quantity	Product Family	Product Type	Fungerer med
---------------	-------------	------------------	----------------	--------------	--------------

21102-857	2 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-853	3 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-854	3 U	100	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-858	4 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-978	5 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-855	6 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-856	6 U	100	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-859	9 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels

ADDITIONAL PRODUCT DETAILS

EMC gaskets (textile) are required for shielding the front panels.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE