

Front Panel, Unshielded, With Fastener Pin

Strømforsyning



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

SERTIFISERINGER



FUNKSJONER

Enable grounding of the front area (protection class 1)

SPESIFIKASJONER

Table 1/3

Katalognummer	Rack Width	Package Quantity	Montering	Front Finish	Rear Finish	Treated Edges
20119-159	7 HP	1	Screw-on Front	Anodized	Conductive	Nei
20119-160	14 HP	1	Screw-on Front	Anodized	Conductive	Nei
20119-161	21 HP	1	Screw-on Front	Anodized	Conductive	Nei
20119-162	28 HP	1	Screw-on Front	Anodized	Conductive	Nei

Katalognummer	Rack Width	Package Quantity	Montering	Front Finish	Rear Finish	Treated Edges
20119-163	42 HP	1	Screw-on Front	Anodized	Anodized	Nei

Table 2/3

Katalognummer	Samsvarer med	EMC Shielding	Høyde	Materiell	Product Type	Rack Height
20119-159	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium	Front Panel	3 U
20119-160	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium	Front Panel	3 U
20119-161	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium	Front Panel	3 U
20119-162	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium	Front Panel	3 U
20119-163	IEC 60297-3-101, IEEE 1101.1/10	Nei	128.4 mm	Aluminium	Front Panel	3 U

Table 3/3

Katalognummer	Type	Bredde
20119-159	Front Panel without Handle	35.2 mm
20119-160	Front Panel without Handle	70.8 mm
20119-161	Front Panel without Handle	106.3 mm
20119-162	Front Panel without Handle	141.9 mm
20119-163	Front Panel without Handle	213 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE