

Varistar CP Cabeling Rack



Welded steel frame for high static load requirements.
Prepared for high cable densities and 19" integration.

CARACTERÍSTICAS

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

ESPECIFICAÇÕES

Product Type: Rack

Material: Aço

Frame Material: Aço

Table 1/3

Número de catálogo	Rack Height	Cladding Material	Frame Color	Altura	Frame Color Code	Cladding Color
10630-028	42U	Aço	Black Grey	2000mm	RAL 7021	Black Grey
10630-027	42U	Aço	Black Grey	2000mm	RAL 7021	Black Grey

Table 2/3

Número de catálogo	Largura	Profundidade	Static Load	Cladding Color Code	Quantidade por embalagem	Dynamic Load
10630-028	800mm	1200mm	1600kg	RAL 7021	1	1000kgf
10630-027	800mm	1200mm	1600kg	RAL 7021	1	1000kgf

Table 3/3

Número de catálogo	Acabamento	Envio rápido
10630-028	Pintura electrostática com Acabamento Texturado	Não
10630-027	Pintura electrostática com Acabamento Texturado	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE