

Varistar CP EMC Shortened Rear Panel with Recessed Mounting Plate



Recessed connection plates are needed for connectors which don't protrude out of the plane of the cabinet

CARACTERÍSTICAS

Intelligent cable management design with recessed connection plates

Connection plate is 400 mm high

For recessed plate: Plate recessed by 40 mm

ESPECIFICAÇÕES

Product Type: Cabinet/Rack Panel

Grau de proteção: IP55

Material: Aço; Stainless Aço

Table 1/1

Número de catálogo	Rack Height	Altura	Largura	Quantidade por embalagem	Acabamento	Envio rápido
21630-909	38U	1800mm	600mm	1	Pintura electrostática com Acabamento Texturado	Não
21630-910	38U	1800mm	800mm	1	Pintura electrostática com Acabamento Texturado	Não

Número de catálogo	Rack Height	Altura	Largura	Quantidade por embalagem	Acabamento	Envio rápido
21630-911	42U	2000mm	600mm	1	Pintura electrostática com Acabamento Texturado	Não
21630-912	42U	2000mm	800mm	1	Pintura electrostática com Acabamento Texturado	Não
21630-913	47U	2200mm	600mm	1	Pintura electrostática com Acabamento Texturado	Não
21630-914	47U	2200mm	800mm	1	Pintura electrostática com Acabamento Texturado	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE