

Varistar CP Heavy-Load Cross Member for seismic frame



Side crossbar to support 19" uprights in a 800 mm wide cabinet supporting 1600 kg static load. The hole pattern allows easy recessment of the 19" plane in 25 mm increments.

CARACTERÍSTICAS

Side crossbar to support 19" uprights in a 800 mm wide reinforced cabinet supporting 1600 kg static load

Hole pattern allows easy recessment of the 19" plane in 25 mm increments

ESPECIFICAÇÕES

Table 1/2						
Número de catálogo	Works With	Material	Acabamento	Cor	Código de cor	Profundidade
24630-155	Varistar CP	Aço	Pintura electrostática com Acabamento Texturado	Black Grey	RAL 7021	1000mm
24630-154	Varistar CP	Aço	Pintura electrostática com Acabamento Texturado	Black Grey	RAL 7021	900mm
24630-152	Varistar CP	Aço	Pintura electrostática com Acabamento Texturado	Black Grey	RAL 7021	600mm

Número de catálogo	Works With	Material	Acabamento	Cor	Código de cor	Profundidade
24630-153	Varistar CP	Aço	Pintura electrostática com Acabamento Texturado	Black Grey	RAL 7021	800mm

Table 2/2

Número de catálogo	Quantidade por embalagem	Unidade de embalagem	Envio rápido
24630-155	4	Pair	Não
24630-154	4	Pair	Não
24630-152	4	Pair	Não
24630-153	4	Pair	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE