


Novastar Frame, Slim-Line

Strømforsyning



Aesthetic aluminum die-cast frame with 200kg static load capacity. Aluminum extruded 19" upright bolted onto the frames.

SERTIFISERINGER



FUNKSJONER

Static load-carrying capacity 200 kg

19" plane - 33 mm at front, 60 mm at rear

Al profile, RAL 7021, incl. grounding

SPESIFIKASJONER

Table 1/2

Katalognummer	Rack Height	Høyde	Bredde	Dybde	Farge	Color Code
---------------	-------------	-------	--------	-------	-------	------------

28230-001	6 U	323 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-060	6 U	323 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-004	9 U	456 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-063	9 U	456 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-007	12 U	589 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-054	12 U	589 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-055	12 U	589 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-066	12 U	589 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-126	12 U	589 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-011	16 U	767 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-070	16 U	767 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-130	16 U	767 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-190	16 U	767 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-191	16 U	767 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-015	20 U	945 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-074	20 U	945 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-134	20 U	945 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-194	20 U	945 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-195	20 U	945 mm	553 mm	1000 mm	Black Grey	RAL 7021

28230-020	25 U	1167 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-079	25 U	1167 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-139	25 U	1167 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-198	25 U	1167 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-199	25 U	1167 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-029	34 U	1567 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-088	34 U	1567 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-148	34 U	1567 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-202	34 U	1567 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-203	34 U	1567 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-033	38 U	1745 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-092	38 U	1745 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-152	38 U	1745 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-206	38 U	1745 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-207	38 U	1745 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-048	43 U	1967 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-097	43 U	1967 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-157	43 U	1967 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-210	43 U	1967 mm	553 mm	900 mm	Black Grey	RAL 7021

28230-211	43 U	1967 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-042	47 U	2145 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-101	47 U	2145 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-162	47 U	2145 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-214	47 U	2145 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-215	47 U	2145 mm	553 mm	1000 mm	Black Grey	RAL 7021

Table 2/2

Katalognummer	Frame Material	Product Type	Statisk belastning	Type
28230-001	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-060	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-004	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-063	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-007	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-054	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-055	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-066	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-126	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-011	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-070	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-130	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line

Katalognummer	Frame Material	Product Type	Statisk belastning	Type
28230-190	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-191	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-015	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-074	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-134	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-194	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-195	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-020	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-079	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-139	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-198	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-199	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-029	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-088	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-148	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-202	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-203	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-033	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line

Katalognummer	Frame Material	Product Type	Statisk belastning	Type
28230-092	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-152	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-206	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-207	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-048	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-097	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-157	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-210	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-211	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-042	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-101	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-162	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-214	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line
28230-215	Aluminium	Cabinet/Rack Frame	200 kgf	Slim-Line

ADDITIONAL PRODUCT DETAILS

Please order doors, rear panels, side panels, top cover assemblies, plinths, floors, shelves, slide rails and castors or adjustable feet separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE