

Varistar CP Plain Steel Door, Seismic IP55, With Multi-Point Locking

Strømforsyning

IP55 Seismic Steel Door with lever handle and multi-Point locking.

FUNKSJONER

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for EMC applications

SPESIFIKASJONER

Table 1/3

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-752	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-753	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-754	38 U	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-2, IEC 61587-2, IEC 60529
21630-755	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-756	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-757	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-758	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-759	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Table 2/3

Katalognummer	Locking Type	Materiell	Product Type	Protection Rating	Rack Width	Type
21630-752	4-Point Locking	Stål	Cabinet Door	IP55		Steel Door, Plain
21630-753	4-Point Locking	Stål	Cabinet Door	IP55	800 HP	Steel Door, Plain
21630-754	4-Point Locking	Stål	Cabinet Door	IP55		Steel Door, Plain
21630-755	4-Point Locking	Stål	Cabinet Door	IP55		Steel Door, Plain
21630-756	4-Point Locking	Stål	Cabinet Door	IP55		Steel Door, Plain
21630-757	4-Point Locking	Stål	Cabinet Door	IP55		Steel Door, Plain
21630-758	5-Point Locking	Stål	Cabinet Door	IP55		Steel Door, Plain
21630-759	5-Point Locking	Stål	Cabinet Door	IP55		Steel Door, Plain

Table 3/3

Katalognummer	Fungerer med
21630-752	Varistar CP
21630-753	Varistar CP
21630-754	Varistar CP
21630-755	Varistar CP
21630-756	Varistar CP

Katalognummer	Fungerer med
21630-757	Varistar CP
21630-758	Varistar CP
21630-759	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE