

Varistar CP Seismic Base Plate, Multi-Piece

Strømforsyning

Multi piece base plate is assembled from inside.

Please order grounding, cover plate, brush strip or filter mat separately.

FUNKSJONER

To cover the base opening

The multi-piece base plate is open at the rear (opening to rear 200 mm deep, no rear opening with 300 mm cabinet depth)

SPESIFIKASJONER

Table 1/2

Katalognummer	Bredde	Dybde	Farge	Color Code	Samsvarer med	Materiell
20630-293	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Stål
20630-294	600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Stål
20630-295	600 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Stål
20630-296	600 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Stål
20630-297	800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Stål
20630-298	800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Stål
20630-299	800 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Stål
20630-300	800 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Stål

Table 2/2

Katalognummer	Product Type	Type	Fungerer med
20630-293	Cabinet/Rack Base	Base Plate, Plain	Varistar CP
20630-294	Cabinet/Rack Base	Base Plate, Plain	Varistar CP
20630-295	Cabinet/Rack Base	Base Plate, Plain	Varistar CP
20630-296	Cabinet/Rack Base	Base Plate, Plain	Varistar CP
20630-297	Cabinet/Rack Base	Base Plate, Plain	Varistar CP
20630-298	Cabinet/Rack Base	Base Plate, Plain	Varistar CP
20630-299	Cabinet/Rack Base	Base Plate, Plain	Varistar CP
20630-300	Cabinet/Rack Base	Base Plate, Plain	Varistar CP

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE