

Varistar CP Seismic Base/Plinth

Strømforsyning

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

FUNKSJONER

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

SPESIFIKASJONER

Table 1/2

Katalognummer	Bredde	Dybde	Farge	Color Code	Samsvarer med	Høyde
21630-110	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-111	600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-112	600 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-113	600 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-114	800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-115	800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-117	800 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm

Katalognummer	Bredde	Dybde	Farge	Color Code	Samsvarer med	Høyde
21630-116	800 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	800 mm

Table 2/2

Katalognummer	Materiell	Product Type	Statisk belastning	Type	Fungerer med
21630-110	Stål	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-111	Stål	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-112	Stål	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-113	Stål	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-114	Stål	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-115	Stål	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-117	Stål	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-116	Stål	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE