


EuropacPRO Cover Plate, Universal



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be used is non-standard boards will be assembled into the subrack.

SERTIFISERINGER



FUNKSJONER

Shielding is provided by optional EMC stainless steel gaskets, between cover plate and side panel

For variable positioning of horizontal rails e.g. for PCBs with non-standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

SPESIFIKASJONER

Materiale:	Aluminium
Produkttype:	Dekkplate
Produktserie:	EuropacPRO
Overflate:	Passivert
Fungerer med:	Delrack
Type:	Universell

Table 1/1

Katalognummer	Rackbredde	Dybde	Antall pakker	Pakkeenhet	Hurtiglevering
24560-031	42HP	175mm	2	Par	Nei

Katalognummer	Rackbredde	Dybde	Antall pakker	Pakkeenhet	Hurtiglevering
24560-032	42HP	235mm	2	Par	Nei
24560-033	42HP	295mm	2	Par	Nei
24560-041	63HP	175mm	2	Par	Nei
24560-042	63HP	235mm	2	Par	Nei
24560-043	63HP	295mm	2	Par	Nei
24560-051	84HP	175mm	2	Par	Nei
24560-052	84HP	235mm	2	Par	Nei
24560-053	84HP	295mm	2	Par	Nei
24560-054	84HP	355mm	2	Par	Nei
24560-055	84HP	415mm	2	Par	Nei
24560-056	84HP	475mm	2	Par	Nei

YTTERLIGERE PRODUKTDETALJER

In addition, 4 contact strips per subrack are required to affix cover to horizontal rail.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE