


# Socket Strip, UTE

## Data Solutions



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with UTE outlets.

### CERTIFICATIONS



### CARACTERISTICI

230 V, 16 A

In accordance with NFC 61-303

Socket strip with UTE sockets

Mounting height 1 U

Horizontal or vertical mounting

Connecting cable 2 m, with SCHUKO/UTE plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

### SPECIFICAȚII

<b>Material:</b>	Aluminiu; Polyamide
<b>Color:</b>	Grey
<b>Product Type:</b>	Socket Strip

Table 1/2

Număr de catalog	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-220	UTE	4	No	230V		1
60110-221	UTE	9	No	230V		1
60110-222	UTE	12	No	230V		1
60110-223	UTE	15	No	230V		1
60110-224	UTE	19	No	230V		1
60110-225	UTE	8	Yes	230V		1
60110-226	UTE	12	Yes	230V		1
60110-227	UTE	8	No	230V	Transient Protection	1
60110-228	UTE	6	No	230V	Overcurrent Protection	1
60110-229	UTE	7	No	230V	Mains Suppression Filter	1
60110-230	UTE	6	No	230V	Fault Current Protection	1
60110-231	UTE	6	No	230V	Fault Current Protection, Overcurrent Protection	1
60110-267	UTE	6	No	230V	Transient Protection, Mains Suppression Filter	1

Table 2/2

Număr de catalog	Depth	Finish	Length
60110-220	44mm	Anodized	210mm
60110-221	44mm	Anodized	438.5mm

Număr de catalog	Depth	Finish	Length
60110-222	44mm	Anodized	947.5mm
60110-223	44mm	Anodized	1202mm
60110-224	44mm	Anodized	1753mm
60110-225	44mm	Anodized	438.5mm
60110-226	44mm	Anodized	947.5mm
60110-227	44mm	Anodized	438.5mm
60110-228	75mm	Anodized	438.5mm
60110-229	44mm	Anodized	438.5mm
60110-230	88mm	Anodized	438.5mm
60110-231	88mm	Anodized	438.5mm
60110-267	44mm	Anodized	438.5mm

## DETALII SUPLIMENTARE DESPRE PRODUS

Please order bracket for vertical mounting separately.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**