

Varistar CP Steel Door, Perforated With Multi-Point Locking

Instalacje zasilające

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

FUNKCJE

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

OKREŚLENIU SPECYFIKACJI

Table 1/2

Numer katalogowy	Rack Height	Wysokość	Szerokość	Kolor	Color Code	Locking Type
21630-533	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-534	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-535	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-536	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-537	33 U	1600 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-538	33 U	1600 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-539	38 U	1800 mm	600 mm	Black Grey	RAL 7021	4-Point Locking

Numer katalogowy	Rack Height	Wysokość	Szerokość	Kolor	Color Code	Locking Type
21630-540	38 U	1800 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-541	42 U	2000 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-542	42 U	2000 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-543	47 U	2200 mm	600 mm	Black Grey	RAL 7021	5-Point Locking
21630-544	47 U	2200 mm	800 mm	Black Grey	RAL 7021	5-Point Locking

Table 2/2

Numer katalogowy	Materiał	Product Type	Typ
21630-533	Stal	Cabinet Door	Steel Door, Perforated
21630-534	Stal	Cabinet Door	Steel Door, Perforated
21630-535	Stal	Cabinet Door	Steel Door, Perforated
21630-536	Stal	Cabinet Door	Steel Door, Perforated
21630-537	Stal	Cabinet Door	Steel Door, Perforated
21630-538	Stal	Cabinet Door	Steel Door, Perforated
21630-539	Stal	Cabinet Door	Steel Door, Perforated
21630-540	Stal	Cabinet Door	Steel Door, Perforated
21630-541	Stal	Cabinet Door	Steel Door, Perforated
21630-542	Stal	Cabinet Door	Steel Door, Perforated
21630-543	Stal	Cabinet Door	Steel Door, Perforated
21630-544	Stal	Cabinet Door	Steel Door, Perforated

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE