

# Internal side panels | Putere și distribuție, MSPS



The galvanised steel internal side panels, MSPS, segregate vertical sections and allow for mounting of busbar supports, MSHS, as well as other accessories. It is a flexible solution both for fix and plug in systems and allows for meeting form 4 segregation according to IEC 61439.

## CARACTERISTICI

Descriere: Internal side panels to build up sections as from the enclosure frame. Frame hole pattern is needed in front, rear, top and bottom.

Material: 1.5 mm galvanized steel.

Livrare: 1 piece with mounting material.

The side panels segregate vertical sections, allowing customer's to mount main busbar supports (MSHS) and other accessories

A flexible solution for both fix and plug-in systems

The side panels allow customers to build up power distribution configurations to meet form 4 segregation according to IEC 61439

Hole patterns are required in the top, bottom, front and rear of the enclosure, in order to mount the internal side panels

## SPECIFICAȚII

**Thickness:** 1.5mm  
**Finish:** Galvanizat  
**Material:** Oțel

Table 1/1

Număr de catalog	Height	Width	Depth	Panel Size	Enclosure Material	Product Family
MSPS1803	1800mm	88.5mm	300mm	1800 x 337mm	Oțel Zincat	Free-Standing
MSPS1805	1800mm	88.5mm	500mm	1800 x 337mm	Oțel Zincat	Free-Standing
MSPS1806	1800mm	26mm	600mm	1800 x 507mm	Oțel Zincat	Free-Standing
MSPS1806F	1800mm	26mm	600mm	1800 x 507mm	Oțel Zincat	Free-Standing
MSPS1808	1800mm	26mm	800mm	1800 x 507mm	Oțel Zincat	Free-Standing
MSPS1808F	1800mm	26mm	800mm	1800 x 507mm	Oțel Zincat	Free-Standing
MSPS2003	2000mm	88.5mm	300mm	2000 x 337mm	Oțel Zincat	Free-Standing
MSPS2005	2000mm	88.5mm	500mm	2000 x 337mm	Oțel Zincat	Free-Standing
MSPS2006	2000mm	26mm	600mm	2000 x 507mm	Oțel Zincat	Free-Standing
MSPS2006F	2000mm	26mm	600mm	2000 x 507mm	Oțel Zincat	Free-Standing
MSPS2008	2200mm	26mm	800mm	2200 x 507mm	Oțel Zincat	Free-Standing
MSPS2008F	2000mm	26mm	800mm	2000 x 507mm	Oțel Zincat	Free-Standing
MSPS2203	2200mm	88.5mm	300mm	2200 x 337mm	Oțel Zincat	Free-Standing
MSPS2205	2200mm	88.5mm	500mm	2200 x 337mm	Oțel Zincat	Free-Standing
MSPS2206	2200mm	26mm	600mm	2200 x 507mm	Oțel Zincat	Free-Standing
MSPS2206F	2200mm	26mm	600mm	2200 x 507mm	Oțel Zincat	Free-Standing

Număr de catalog	Height	Width	Depth	Panel Size	EnclosureMaterial	Product Family
MSPS2208	2200mm	26mm	800mm	2200 x 507mm	Oțel Zincat	Free-Standing
MSPS2208F	2200mm	26mm	800mm	2200 x 507mm	Oțel Zincat	Free-Standing

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**