

Front Panel EMC Textile Shielding Kit, -40... +70°C, 6 U; 10 pieces

NUMER KATALOGOWY

21101-855



The textile EMC gaskets are inserted into a slot on the right hand side of the U-shaped front panels. The gaskets are glued to the front panel.

CERTYFIKATY



FUNKCJE

Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.

Profile seal is bonded onto the contact surface of the 19" bracket or of the rear angle and sets up the conductive connection to the U-shaped front panels

Temperature range -40 °C ... +70 °C

ATRYBUTY PRODUKTU

Wysokość stojaka: 6U

Liczba opakowań: 10

Głębokość (D): 1.62mm

Wysokość (H): 232mm

Materiał: Elastomer termoplastyczny

Rodzina produktów: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; PropacPRO; Moduł wtykowy typu ramowego

Typ produktu: Zestaw ekranujący

Szerokość (W): 3.8mm

Współpracuje z: Stojaki podrzędne; Obudowy; Panele przednie

Klasyfikacja palności: UL® 94V-0

DODATKOWE INFORMACJE O PRODUKCIE

EMC gaskets (textile) are required for shielding the front panels.

SCHEMATY



OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE