


VPX Backplane, 3 U, 7 Slots, BKP3-CEN07-15.2.3-4, RTM

NUMER KATALOGOWY

23001-815



The nVent SCHROFF VPX Backplane have excellent Signal Integrity for highest data transfer rates.

CERTYFIKATY



FUNKCJE

In accordance with: VITA 46.0 VPX base standard; VITA 46.3 Serial RapidIO on VPX; VITA 46.4 PCI Express on VPX Fabric Connector; VITA 46.7 Ethernet on VPX Fabric Connector; VITA 46.11 System Management for VPX

DIP switch for system slot settings

JTAG connections

Lockable aux utility and sense connectors

M4 power studs for power supply, max. 22 A per slot for each voltage

ATRYBUTY PRODUKTU

Typ produktu: Płyta montażowa

Liczba szczelin: 7

Wysokość stojaka: 3U

Typ płyty montażowej: VPX, VITA 65

Szerokość szczeliny: 5HP

Typ złącza: MultiGig

Typ złącza zasilania: Słupki Powerstud M4

Typ złącza mediów: Microfit, 8-stykowe

Szerokość: 186.46mm

Liczba opakowań: 1

DODATKOWE INFORMACJE O PRODUKCIE

Other VPX Backplanes and custom VPX Backplane designs on request.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE