

T-Series Horizontal Splice Kit, Side Fill



T-Series splice kits contain the following: Sleeve, filler material kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), pouring basin and pouring basin crucible. Splice kits are ordered based on the quantity of splices needed. Sleeves and filler material kits are one-time use parts. Pouring basins and crucibles are prorated based on their anticipated life. Ordering splice kits simplifies ordering, reduces order errors and helps ensure proper sizing of components. Kits can be ordered with longer (extended) sleeves for use when the reinforcing steel deformation pattern or spacing does not meet the minimum product specifications.

CARACTERISTICI

Simplifies ordering

Used to splice the same diameter bars

SPECIFICAȚII

Sleeve: Standard Length

Table 1/2

Număr de catalog	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Length 1 (L1)	Length 2 (L2)	Height 1 (H1)
RBT8101HS	25 mm	#8	25M	84 mm	403 mm	464mm
RBT1891HS	57 mm	#18	55M	102 mm	423 mm	533mm
RBT11101HS	36 mm	#11	35M	94 mm	413 mm	502mm
RBT1091HS	32 mm	#10		88 mm	407 mm	502mm
RBT6101HS	20 mm	#6	20M	84 mm	397 mm	464mm
RBT9101HS	28 mm	#9	30M	88 mm	407 mm	464mm

Table 2/2

Număr de catalog	Height 2 (H2)	Diameter (Ø)
RBT8101HS	75mm	102 mm
RBT1891HS	75mm	178 mm
RBT11101HS	75mm	127 mm
RBT1091HS	75mm	127 mm
RBT6101HS	75mm	102 mm
RBT9101HS	75mm	102 mm

DETALII SUPLIMENTARE DESPRE PRODUS


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

All dimensions are for reference only.

Components can also be purchased separately: (1) Sleeve, (2) Filler Material Kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), (3) Pouring Basin, and (4) Pouring Basin Crucible.

Splice Kit Components							
Splice Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube	Sleeve	Pouring Basin	Pouring Basin Crucible
RBT6101HS	RBF50	RBS35477	RBS5037	RBS5038	RBT6101HSA	RBWS1547X	RBWS22774
RBT8101HS	RBF55	RBS354710	RBS5037	RBS5038	RBT8101HSA	RBWS1547C	RBWS22774
RBT9101HS	RBF80	RBS354711	RBS5037	RBS5038	RBT9101HSA	RBWS1547D	RBWS22774
RBT1091HS	RBF90	RBS354712	RBS5037	RBS5038	RBT1091HSA	RBWS1547E	RBWS22775
RBT11101HS	RBF105	RBS354712	RBS5037	RBS5038	RBT11101HSA	RBWS1547F	RBWS22775
RBT1891HS	RBF270	RBS354720	RBS5037	RBS5039	RBT1891HSA	RBWS1547M	RBWS22777

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE