


EuropacPRO Cover Plate for Bolting to Side Panel

Power Utilities



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be screwed onto the side panel.

CERTIFICATIONS



CARACTERISTICI

For variable positioning of horizontal rails e.g. for PCBs with standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

SPECIFICAȚII

Table 1/2

Număr de catalog	Rack Width	Depth	Package Quantity	Product Family	Product Type	Type
24560-064	42 HP	175 mm	1	EuropacPRO	Cover Plate	Perforated
24560-065	42 HP	235 mm	1	EuropacPRO	Cover Plate	Perforated

Număr de catalog	Rack Width	Depth	Package Quantity	Product Family	Product Type	Type
24560-066	42 HP	295 mm	1	EuropacPRO	Cover Plate	Perforated
24560-071	63 HP	175 mm	1	EuropacPRO	Cover Plate	Perforated
24560-072	63 HP	235 mm	1	EuropacPRO	Cover Plate	Perforated
24560-073	63 HP	295 mm	1	EuropacPRO	Cover Plate	Perforated
24560-078	84 HP	175 mm	1	EuropacPRO	Cover Plate	Perforated
24560-079	84 HP	235 mm	1	EuropacPRO	Cover Plate	Perforated
24560-080	84 HP	295 mm	1	EuropacPRO	Cover Plate	Perforated
24560-081	84 HP	355 mm	1	EuropacPRO	Cover Plate	Perforated
24560-082	84 HP	415 mm	1	EuropacPRO	Cover Plate	Perforated
24560-083	84 HP	475 mm	1	EuropacPRO	Cover Plate	Perforated
24560-061	42 HP	275 mm	1	EuropacPRO	Cover Plate	Perforated
24560-062	63 HP	275 mm	1	EuropacPRO	Cover Plate	Perforated
24560-063	84 HP	275 mm	1	EuropacPRO	Cover Plate	Perforated
24579-090	42 HP	277.75 mm	1	EuropacPRO	Cover Plate	Perforated
24579-092	84 HP	277.75 mm	1	EuropacPRO	Cover Plate	Perforated

Table 2/2

Număr de catalog	Works With	Package Unit	Torque
24560-064	Subracks	Pair	2.1 N·m
24560-065	Subracks	Pair	2.1 N·m

Număr de catalog	Works With	Package Unit	Torque
24560-066	Subracks	Pair	2.1 N·m
24560-071	Subracks	Pair	2.1 N·m
24560-072	Subracks	Pair	2.1 N·m
24560-073	Subracks	Pair	2.1 N·m
24560-078	Subracks	Pair	2.1 N·m
24560-079	Subracks	Pair	2.1 N·m
24560-080	Subracks	Pair	2.1 N·m
24560-081	Subracks	Pair	2.1 N·m
24560-082	Subracks	Pair	2.1 N·m
24560-083	Subracks	Pair	2.1 N·m
24560-061	Subracks	Pair	
24560-062	Subracks	Pair	
24560-063	Subracks	Pair	
24579-090	Subracks	Pair	2.1 N·m
24579-092	Subracks	Pair	2.1 N·m

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE